

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

1800 Grooves/mm, 12.5 x 25mm, UV Holographic Grating



Reflective Holographic Gratings

Stock #43-218 3-4 DAYS



1



€131,00

ADD TO CART

Qty 1-10

€131,00

Qty 11+

€114,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
1800

Wavelength Range (nm):
250 - 400

Dimensions (mm):

12.5 x 25.0 ±0.5
Coating: Bare Aluminum
Construction: Holographic Grating
Length (mm): 25.00
Substrate:  Float Glass
Thickness (mm): 9.50 ±0.5
Type: Reflective Diffraction Grating
Wavelength: UV
Width (mm): 12.50
Alignment of Grooves to Edge (°): ±0.5
Absolute Peak Efficiency, Typical (%): 78
Peak Efficiency Avg, Typical (%): >69

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View