

1.8mm FL, No IR-Cut Filter, f/2, Micro Video Lens



Stock #36-182 3-4 DAYS

- 1 + **€59,00**

ADD TO CART

Qty 1-49
€59,00
Qty 50+
€47,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm): 15.70
Maximum Diameter (mm): 15.0
Maximum Image Circle (mm): 4.50
Horizontal Field of View @ Max Sensor Format:

122
Resolution, On-Axis: 160 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 80 lp/mm @ 20% Contrast
Resolution, Full Field: 107 lp/mm @ 20% Contrast
Note: Standard
Type: M12 Imaging Lens
Focal Length FL (mm): 1.80
Maximum Sensor Format: 1/4"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/2
Distortion (%): -76.2
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View