

5mW, 635nm Laser Bat Power ZAT



Stock **#19-444** **1 In Stock**

- 1 + €258⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	€258,00 each
Qty 10+	€232,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes



General

Elliptical Dot
Style:
3R
Laser Class - CDRH:

Physical & Mechanical Properties

162
Weight (g):
124.00
Length (mm):

Optical Properties

635.00
Wavelength (nm):
Red
Color:
Up to 2,000mm
Focus Range (mm):

Electrical

5
Output Power (mW):

Hardware & Interface Connectivity

1 AA Battery (Not Included)
Power Requirement:
Free Space
Output Type:

Environmental & Durability Factors

IP40
Environmental Rating:

Regulatory Compliance

[View](#)
Certificate of Conformance:

Product Details

- Bright Red 635nm Wavelength
- Line, Crosshair, or Dot Projection
- Battery Powered Operation with a Fixed Focus
- Sturdy, Metal Housing

Z-Laser ZAT Battery Powered Lasers are ideal for positioning and alignment applications. Their battery powered design provides maneuverability by removing the need for a fixed power supply. IP40 rated, shock proof, and vibration proof with a sturdy, metal housing makes these lasers excellent for harsh environments and repeated use. Z-Laser ZAT Battery Powered Lasers are suitable for use in industrial environments such as Automotive, Paper, Wood, Ceramic, and Metal. Available with 1 or 5mW output powers, the lasers utilize one AA battery (not included) ensuring easy maintenance and an extended lifetime.