

TECHSPEC®

1" Dia. Protected Silver, $\lambda/20$ Flat Fused Silica



Stock **#43-408-577** 3-4 DAYS

-

1

+

€208,00

ADD TO CART

Qty 1-10

€208,00

Qty 11+

€187,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
 $\lambda/20$ (measured before coating)

Back Surface:
Commercial Polish

Surface Quality: 60-40
Diameter (mm): 25.40 +0.0/-1.02
Diameter Tolerance (inches): +0.0/-0.04
Substrate: □ Fused Silica (Corning 7980)
Coating Specification: R _{avg} >98% @450 - 2000nm R _{avg} >98% @2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 22.86
Note: Flatness is specified as Peak to Valley
Thickness (mm): 12.70 ±1.5
Thickness Tolerance (mm): ±1.5
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 10
Wavelength Range (nm): 450 - 10000
Damage Threshold, Reference: □ 0.5 J/cm² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant