

1" Travel, Eng Micrometer, Solid-Top Ball Bearing Stage



32mm/1.25" Center drive stage and its X-Y-Z configuration



Stock #37-935 [CONTACT US](#)

1 **€521,00**

ADD TO CART

Qty 1+

€521,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
English Micrometer

Drive Orientation:
Center Drive

Type:
English

Stage Size (mm):
44.4 x 44.4

Travel (inches):
1

Construction:
Aluminium Stage

Graduation (inches):
0.001

Height (inches):
0.75

Height (mm):
19.1

Load Capacity, Normal (lbs):
25

Note:
Solid Top

Stage Size (inches):
1.75 x 1.75

Straight Line Accuracy (inches):
0.00008/inch of travel

Weight (lbs):
0.5

Thrust Capacity, T_a (lbs):
10

Thrust Capacity, T_b (lbs):
5

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)