

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

1" X 1" (200 lp/mm), Ronchi Ruling



Stock #58-781 3-4 DAYS



1



€508,00

ADD TO CART

Qty 1-4

€508,00

Qty 5+

€483,60

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:
Vacuum Deposited Chrome, OD >3.0

Dimensional Tolerance (inches):
±0.02

Frequency (lp/mm):
200

Substrate:

Float Glass
Optical Density OD (Average): 3.00
Dimensions (inches): 1 x 1
Surface Quality: 60-40
Thickness (mm): 1.50
Type: Metric
Dimensional Tolerance (mm): ± 0.02
Line to Line Parallelism (arcsec): ≤2
Parallelism of Pattern to Substrate (°): ±1
Surface Flatness (P-V): 1λ

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View