

1" x 1" (60 lp/mm), Ronchi Ruling



Stock #66-348 CLEARANCE **20+ In Stock**

€331⁹⁵

ADD TO CART

Volume Pricing	
Qty 1+	€331,95 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Metric Type:

Physical & Mechanical Properties

±0.02 Dimensional Tolerance (inches):

1 x 1 Dimensions (inches):

1.50 Thickness (mm):

Dimensional Tolerance (mm):
± 0.02

Line to Line Parallelism (arcsec):
≤ 2

Parallelism of Pattern to Substrate (°):
± 1

Optical Properties

Coating:
Vacuum Deposited Chrome, OD >3.0

Frequency (lp/mm):
60

Substrate: □
Float Glass

Optical Density OD (Average):
3.00

Surface Quality:
20-10

Surface Flatness (P-V):
1λ

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 240:
[Compliant](#)

Product Details

- Chrome on Glass
- High Tolerance
- Superior to Etched and Filled Rulings
- Lines Parallel to Edge
- English and Metric Versions Available

High Precision Ronchi Rulings are excellent for evaluating resolution, field distortion, and parfocal stability. The glass targets are coated with vacuum-deposited chrome and have a float glass substrate. English and Metric version are available with various Linepairs Per Inch (LPI) and Linepairs Per Millimeter (lp/mm) measurements. High Precision Ronchi Rulings are offered in 0.5", 1", 2", and 4" squares.