

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #58-198 ☐ In Stock



1



€772,00

ADD TO CART

Qty 1-4

€772,00

Qty 5+

€734,30

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:
Vacuum-Deposited Durable Chromium

Substrate:
Float Glass

Optical Density OD (Average):
≥3.0

Resolution:

Minimum: Group 0, Element 1 Maximum: Group 9, Element 3
Dimensions (inches): 2 x 2 ±0.04
Surface Quality: 20-10
Thickness (mm): 1.50 ±0.05
Type: Positive Target
Edges: Beveled
Flatness (mm): ≤0.00254
Note: Pattern Location is Centered
Options: High Resolution
NIST Certification: No

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View