

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #19-916 3-4 DAYS



1



€520,00

ADD TO CART

Qty 1-10

€520,00

Qty 11+

€470,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
200.00 +0.0/-0.5

Effective Focal Length EFL (mm):
600.00 @ 587.6nm

Back Focal Length BFL (mm):
586.00

Coating:

MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 120-80
Center Thickness CT (mm): 21.60
Edge Thickness ET (mm): 5.03
Radius R₁ (mm): 310.00
Clear Aperture CA (mm): 195
f#: 3.00
Numerical Aperture NA: 0.17
Type: Condenser Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant