

20" x 24" UV Filter Sheet



Stock **#39-426** 20+ In Stock

-

1

+

€29^{.50}

ADD TO CART

Volume Pricing	
Qty 1+	€29,50 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Longpass Filter

Type:

Physical & Mechanical Properties

508.0 x 609.6

Dimensions (mm):

609.60

Length (mm):

20 x 24

Dimensions (inches):

508.00	Width (mm):
Optical Properties	
400.00	Cut-On Wavelength (nm):
Polyester Film	Substrate:
Clear	Color:
200 - 750	Wavelength Range (nm):
Regulatory Compliance	
Compliant	Reach 191:
Compliant	RoHS 2015:
View	Certificate of Conformance:

Product Details

- Virtually Transparent, Flexible Polyester Filter
 - Deep-Dyed PET Substrate to Absorb UVA, UVB, and UVC Rays
 - <10% Transmission Below 390nm
- Flexible Thin Film UV Filters block UVA, UVB, and UVC wavelengths while transmitting visible illumination. These filters are ideal for applications where ultraviolet rays have harmful effects.

Technical Information

