

20X EO M Plan Apo Long Working Distance Infinity Corrected



50XEO MPlan Apo Long Working Distance Infinity Corrected, #59-879

Stock **#59-878** 3-4 DAYS

- 1 + **€2.098,00**

ADD TO CART

Qty 1+
€2.098,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View (mm):
1.2

Horizontal Field of View, 1/2" Sensor:
0.32mm

Horizontal Field of View, 2/3" Sensor:
0.44mm

Horizontal Field of View, 1" Sensor:
0.64mm

Focal Length FL (mm):

10.00
Length (mm): 75.00
Length excluding Threads (mm): 75.00
Magnification: 20X
Maximum Diameter (mm): 34
Numerical Aperture NA: 0.42
Mounting Threads: M26 x36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 0.7
Depth of Field (µm): 1.60
Field of View, 24 Diameter Field Eyepiece (mm): 1.2
Operating Temperature (°C): +10 to +40
Operating Humidity: <85% with no condensation
Working Distance (mm): 20.0
Weight (g): 320
Wavelength Range (nm): 390 - 780
Style: Infinity Corrected
Field Number (mm): 24
Parfocal Length (mm): 95
Immersion Liquid: N/A

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View