

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® Z1 X 30mm Enhanced Aluminum, λ /4 Mirror



Stock #43-507 ☒ In Stock



1



€55,00

ADD TO CART

Qty 1-5

€55,00

Qty 6+

€44,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
 λ /4

Substrate: ☐
[BOROFLOAT®](#)

Back Surface:
Ground

Surface Quality: 60-40
Dimensions (mm): 21.0 x 30.0
Dimensional Tolerance (mm): +0/-0.5
Coating Specification: R _{avg} >95% @450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 5.00 +0.5/-0
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Length (mm): 30.00
Width (mm): 21.00
Damage Threshold, Reference: ☐ 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant