

2.25" x 2.70", 2.0" FL, Cylinder Fresnel Lens



Cylinder Fresnel Lenses

Stock **#46-112** **3 In Stock**

-

1

+

€70^{.50}

ADD TO CART

Volume Pricing	
Qty 1-10	€70,50 each
Qty 11-49	€63,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Fresnel Lens	Type:
Physical & Mechanical Properties	
0.06	Center Thickness CT (inches):
±0.05	Dimensional Tolerance (inches):

2.25 x 2.7	Dimensions (inches):
57.15 x 68.58	Dimensions (mm):
2.0 x 2.7	Effective Size (inches):
±0.020	Thickness Tolerance (inches):

Optical Properties

50.80	Effective Focal Length EFL (mm):
Acrylic	Substrate: ☐
Uncoated	Coating:
400 - 1100	Wavelength Range (nm):
2.00	Effective Focal Length EFL (inches):
200.00	Groove Density (grooves/inch):
1.49	Index of Refraction (n _d):
85 (Typical)	Transmission (%):

Environmental & Durability Factors

80 (Maximum)	Operating Temperature (°C):
--------------	-----------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:

Product Details

- Collapsed Version of a Standard Cylinder Lens
- Ideal for Focusing One Dimension
- Various Sizes Available

Technical Information

