

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



22mm CAC-Mount Longpass Glass Color Filter

Stock #13-030 3-4 DAYS



1



€93,00

ADD TO CART

Qty 1-9

€93,00

Qty 10+

€83,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):

25.40 ±0.38

Clear Aperture CA (mm):

22.0

Cut-Off Position λ_c (nm):

550±6

Cut-On Wavelength (nm): 550.00
Density (g/cm³): 2.56
Glass/Filter Number: SCHOTT OG550
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Orange
Passband Limit 1 λ_{p1} (nm): 620.00
Spectral Transmittance t_p (%): 93.00
Stopband Limit λ_s(nm): 480.00
Surface Quality: 80-50
Transformation Temperature (°C): 507.00
Type: Longpass Filter
Wavelength: VIS
Reflection Factor P_d: 0.92
Substrate Thickness (mm): 3.00 ±0.2
Thread Type: C-Mount
Total Length (mm): 20.3
Mount Diameter (mm): 30.0
Filter Included: #32-754
Mount Included: #56-353

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View