

2/3" Format C-Mount Fisheye Lens 1.8mm FL



Stock **#62-274** ☐ In Stock



1



€820,00

ADD TO CART

Qty 1+

€820,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Variable

Length (mm):
52.10

Horizontal Field of View, 1/2" Sensor:
185°

Maximum Diameter (mm):
56.5

Weight (g):
135.00

Maximum Image Circle (mm): 11.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 1.80
Maximum Sensor Format: 2/3"
Working Distance (mm): 100 - ∞
Mount: C-Mount
Aperture (f/#): f/1.4 - f/16
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View