

TECHSPEC® 25 x 35mm UV Enhanced Aluminum, λ/4 Mirror



Stock **#46-719** ☒ In Stock

-

1

+

€62,50

ADD TO CART

Qty 1-5
€62,50
Qty 6+
€50,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate: ☐
[BOROFLOAT®](#)

Back Surface:
Fine Ground

Surface Quality: 60-40
Dimensions (mm): 25.0 x 35.0
Dimensional Tolerance (mm): +0.0/-0.5
Coating Specification: R_{avg} >89% @ 250 - 450nm R_{avg} >85% @ 250 - 700nm
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 5.00 +0.5/-0.0
Type: Flat Mirror
Wavelength Range (μm): 0.25 - 0.7
Wavelength Range (nm): 250 - 700
Length (mm): 35.00
Width (mm): 25.00
Damage Threshold, Reference:  0.5 J/cm² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant