

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #21-320 3-4 DAYS

-

1

+

 €49,50

ADD TO CART

Qty 1-9

€49,50

Qty 10+

€44,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Effective Focal Length EFL (mm):
-50.00

Substrate: ☐ N-BK7
f#: 1.00
Numerical Aperture NA: 0.25
Coating: YAG-BBAR (500-1100nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 500 - 1100
Back Focal Length BFL (mm): -52.31
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.50 ±0.10
Centering (arcmin): <1
Clear Aperture CA (mm): 24.00
Coating Specification: R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm
Edge Thickness ET (mm): 6.33
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -25.84
Surface Quality: 40-20
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant