

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #49-534 3-4 DAYS

[Other Coating Options](#)



1



€44,50

ADD TO CART

Qty 1-9

€44,50

Qty 10+

€40,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-25.00
Substrate: NSF11
f#: 1.00
Numerical Aperture NA: 0.50
Coating: NIR I (600-1050nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 600 - 1050
Back Focal Length BFL (mm): -26.96
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <1
Clear Aperture CA (mm): 24.00
Coating Specification: Ravg ≤0.5% @ 600 - 1050nm
Edge Thickness ET (mm): 7.75
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -19.62
Surface Quality: 40-20
Damage Threshold, By Design: 7 J/cm² @ 1064nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant