

TECHSPEC® 25/25.4mm Sq. Kinematic Mount, 3 Screws



25/25.4mm Sq. Kinematic Mount, 3 Screws, #58-860

Stock **#58-860** 3-4 DAYS

⊖ 1 ⊕ **€105,00**

ADD TO CART

Qty 1-4

€105,00

Qty 5+

€94,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Adjustable - Tip-Tilt

Type of Optics:
Square

Size of Compatible Optics (mm):
25.0 - 25.4

Number of Adjustment Screws: 3
Clear Aperture CA (mm): 22.9 x 22.9
Travel (mm): Z-Axis: 8
Construction: Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings
Angle Tolerance (°): 0.4 per 0.25mm turn
Fine Tilt Angle (°): ±5
Fine Tip Angle (°): ±5
Sensitivity per 1° Knob Rotation (arcsec): 4
Thermal Stability (μrad): <5
Adjustment Screw Pitch (mm): 0.25
Compatible Post: M4 x0.7, 8-32
Min. Thickness of Compatible Optics (mm): 1.0
Pointing Stability (μrad): 1.3

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View