

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

25.4mm Clear Aperture, 2 Arcsec, Aluminum Retroreflector



Stock #46-173 3-4 DAYS



1



€1.025,00

ADD TO CART

Qty 1+

€1.025,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Beam Deviation (arcsec):
2.00

Clear Aperture CA (mm):
25.4

Coating:
Enhanced Aluminum (450-650nm)

Diameter (mm):
41.30

Exiting Wavefront Accuracy:
0.25λ

Substrate: 

Surface Quality:
80-50

Mounting Threads:
(2) ¼-20, M6 x 1.0

Type:
Retroreflector

Dimensional Tolerance (mm):
±1.6

Image Orientation:
Left-Handed

Ray Deviation (°):
180

Wavelength Range (nm):
400 - 700

Regulatory Compliance

RoHS 2015:
Compliant

REACH 201:
Compliant

Certificate of Conformance:
[View](#)