

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC X10 Laser Line Coated Windows

Stock #19-737 CLEARANCE 3-4 DAYS



1



€146,95

ADD TO CART

Qty 1+

€146,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):

0

Clear Aperture CA (mm):

22.86

Coating:

Laser V-Coat (261.4nm)

Design Wavelength DWL (nm):

261.4

|                                                                                           |
|-------------------------------------------------------------------------------------------|
| <div>Diameter (mm):<br/>25.40 +0.00/-0.10</div>                                           |
| <div>Substrate: <div>Fused Silica</div> (Coming 7980)</div>                               |
| <div>Index of Refraction <math>n_d</math>:<br/>1.458</div>                                |
| <div>Surface Quality:<br/>10-5</div>                                                      |
| <div>Thickness (mm):<br/>6.35 ±0.20</div>                                                 |
| <div>Type:<br/>Laser Line Window</div>                                                    |
| <div>Parallelism (arcmin):<br/>&lt;3</div>                                                |
| <div>Bevel:<br/>Protective as needed</div>                                                |
| <div>Clear Aperture (%):<br/>90</div>                                                     |
| <div>Abbe Number (<math>v_d</math>):<br/>67.8</div>                                       |
| <div>Coating Specification:<br/>R<sub>abs</sub> &lt;0.25% @ 261.4nm</div>                 |
| <div>Surface Flatness (P-V):<br/>λ/10</div>                                               |
| <div>Damage Threshold, By Design: <div>3 J/cm<sup>2</sup> @ 266nm, 20ns, 20Hz</div></div> |
| <div>Edges:<br/>Fine Ground</div>                                                         |
| <div>Type of Window:<br/>Glass</div>                                                      |

## Regulatory Compliance

|                                                 |
|-------------------------------------------------|
| <div>RoHS:<br/>Compliant</div>                  |
| <div>Certificate of Conformance:<br/>View</div> |