

TECHSPEC® 25.4mm Dia., 3.18mm Thick, Fused Silica Uncoated Laser Window Substrate



TECHSPEC® Uncoated Laser Window Substrates

Stock #37-694 3-4 DAYS

⊖ 1 ⊕ **€145,00**

ADD TO CART

Qty 1-5

€145,00

Qty 6+

€130,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
22.86

Coating:
Uncoated

Diameter (mm):
25.40 +0.00/-0.10

Substrate: [Fused Silica](#) (Corning 7980)

Index of Refraction n_d :
1.458

Surface Quality:
10-5

Thickness (mm):
3.18 ±0.20

Type:
Laser Window Substrate

Parallelism (arcmin):
<3

Bevel:
Protective as needed

Clear Aperture (%):
90

Abbe Number (v_d):
67.8

Wavelength Range (nm):
200 - 2200

Surface Flatness (P-V):
λ/10

Fused Silica Grade:
7980 0F

Edges:
Fine Ground

Type of Window:
Glass

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)