

TECHSPEC® 25.4mm Dia., 532nm T, 1064nm R 0° Harmonic Separator



TECHSPEC Nd:YAG Harmonic Separators

Stock **#22-675** 3-4 DAYS



1



€268,00

ADD TO CART

Qty 1-5

€268,00

Qty 6+

€241,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
0

Clear Aperture (%):
>85

Coating Specification:
Surface 1: R_{abs}: >99% @ 1064nm, T_{abs}: >95% @ 532nm

Surface 2: R _{abs} : <0.5% @ 532nm
Construction: Dichroic
Diameter (mm): 25.40 +0.00/-0.10
Parallelism (arcmin): <3
Reflection Wavelength (nm): 1064
Substrate:  Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/10
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Transmission Wavelength (nm): 532
Type: Harmonic Beamsplitter
Damage Threshold, By Design:  Surface 1: 7.5 J/cm ² @ 1064nm, 20ns, 20Hz 7.5 J/cm ² @ 532nm, 20ns, 20Hz Surface 2: 10 J/cm ² @ 532nm, 20ns, 20Hz

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View