

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

25.4mm Dia. 670nm $\lambda/4$ Quartz waveplate Zero Order



Stock #46-552 CLEARANCE 3-4 DAYS



1



€488,00

ADD TO CART

Qty 1-5

€488,00

Qty 6+

€395,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
15.00

Coating:
Laser V-Coat (670nm)

Design Wavelength DWL (nm):
670

Diameter (mm):

25.40 +0.00/-0.25
Substrate: Crystal Quartz
Retardance: $\lambda/4$
Surface Quality: 10-5
Thickness (mm): 7.80 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: $\lambda/10$ for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: $\pm \lambda/200$
Temperature Coefficient ($\lambda/^\circ\text{C}$): 0.0001
Retardance Order: 0

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View