

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



UltraFast Innovations (UFI) Positive Dispersion Ultrafast Mirrors

Stock #17-069 [CONTACT US](#)



1



€788,00

ADD TO CART

Qty 1-9

€788,00

Qty 10+

€711,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Wedge (arcmin):
10

Clear Aperture (%):
80

Back Surface:

Commercial Polish
Coating Specification: R _{avg} >99.5% @ 700 - 1100nm (5° AOI, p-polarization)
GDD Specification: +100fs ² @ 700 - 1100nm (5° AOI, p-polarization)
Wavelength Range (nm): 700 - 1100
Irregularity (P-V) @ 632.8nm: λ/10
Coating Type: Dielectric
Coating: Positive Dispersion (700-1100nm)
Diameter (mm): 25.40 +0.00/-0.05
Thickness (mm): 6.35 ±0.20
Angle of Incidence (°): 5
Substrate: ☐ Fused Silica (Corning 7980)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant