

25.4mm Dia. 980nm $\lambda/2$ Quartz Waveplate Zero Order



Stock **#46-557** [CONTACT US](#)

- 1 + **€488,00**

ADD TO CART

Qty 1-5
€488,00
Qty 6+
€395,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
15.00

Coating:
Laser V-Coat (980nm)

Design Wavelength DWL (nm):
980

Diameter (mm):

25.40 +0.00/-0.25
Substrate: Crystal Quartz
Retardance: λ/2
Surface Quality: 10-5
Thickness (mm): 7.80 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: λ/10 for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: ±λ/200
Temperature Coefficient (λ/°C): 0.0001
Retardance Order: 0

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View