

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Molded Acrylic Aspheric Lenses



Stock **#48-185** 3-4 DAYS



1



€65,00

ADD TO CART

Qty 1-10

€65,00

Qty 11+

€53,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.40 ±0.1

Effective Focal Length EFL (mm):
152.00 @632.8nm

Numerical Aperture NA: 0.08
Back Focal Length BFL (mm): 149.1
Substrate: ☐ PMMA
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 632.8
Coating: BBAR (450-650nm)
Coating Specification: R _{avg} <0.5% @ 450 - 650nm
Clear Aperture CA (mm): 23.9
Edge Thickness ET (mm): 4.00
Center Thickness CT (mm): 4.96
f/#: 6.00
Bevel: Protective bevel as needed
Operating Temperature (°C): 80.00
Radius R (mm): 74.68
Type: Aspheric Lens
Wavelength Range (nm): 450 - 650
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View