

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

25.4mm Diameter Unmounted 0.04-3.0 OD, Circular variable Neutral Density (ND) Filter



Unmounted Circular Variable Neutral Density (ND) Filters

Stock #43-761 3-4 DAYS



1



€278,00

ADD TO CART

Qty 1-10

€278,00

Qty 11+

€250,20

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
0.00

Optical Density OD (Average):
0.04 - 3.0

Substrate: ☐
[B270](#)

Inner Diameter (mm): 7.5
Coating: Variable
Outer Diameter (mm): 25.4
Surface Quality: 60-40
Thickness (mm): 1.52
Thickness Tolerance (mm): ±0.25
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Parallelism (arcmin): ±3
Dimensional Tolerance (mm): ±0.10 ID, ±0.20 OD
Optical Density Tolerance (%): ±5
Linearity (%): ±5
Coating Specification: Continuously Variable Inconel from 0 - 270°
Mount: Unmounted

Regulatory Compliance

Reach 181: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View