

TECHSPEC®

25.4mm H x 25.4mm L x 200mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #35-027 3-4 DAYS

- 1 + **€70,00**

ADD TO CART

Qty 1-5
€70,00

Qty 6+
€56,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
200.00

Substrate: ☐
[N-BK7](#)

f#:

7.8740157480315
Numerical Aperture NA: 0.06
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 198.38
Center Thickness CT (mm): 2.10
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.4 x 25.4
Edge Thickness ET (mm): 1.31
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 103.36
Surface Quality: 60-40

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View