

TECHSPEC 25.4mm Kinematic Mount



25.4mm Kinematic Mount, #85-695

Stock **#85-695** **9 In Stock**

⊖ 1 ⊕ €196.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€196,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Tip-Tilt **Function:**

Circular **Type of Optics:**

Accepts 25/25.4mm Diameter Optics **Note:**

Physical & Mechanical Properties

Compatible Plate Inner Diameter (mm):

30.0

Inner Diameter (mm):

25.4

Construction:

Black Anodized Aluminum

Through Hole Diameter (mm):

12.7

Dimensions (mm):

30 Dia.

Adjustment Screw Pitch (mm):

0.5

Travel (°):

±8 Tip/Tilt

Threading & Mounting

Size of Compatible Optics (mm):

25.0 - 25.4

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 235:

[Compliant](#)

Product Details

- Available for a Range of Optical Components
- Anodized Aluminum Construction with Stainless Steel Screws
- 0.5mm Pitch Fine Adjustment Screw
- [Fixed Optical Mounts](#) Also Available

Ideal for beam steering applications, TECHSPEC® Cage System Adjustable Optical Mounts are used to integrate a variety of optical components into a TECHSPEC Cage System. Designed to fit within the inner diameter of 25mm or 30mm standard [cage system plates](#), these optical mounts utilize set screws to secure optical components in place, providing the stability and adjustment needed for precision optical alignment. [#85-695](#) 25.4mm Kinematic Mount features a 12.7mm clear aperture and can be paired with [#85-699](#) 45° plate beamsplitter mount.