

25.0/25.4mm Optic Diameter, X-Y Translating Quick Start Optical Mounts



#17-513: 25.0/25.4mm Optic Diameter, X-Y Translating Mounts



Stock **#17-513** [CONTACT US](#)

- 1 +

€294,60

ADD TO CART

Qty 1+
€294,60

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Adjustable - Linear (XY)

Type of Optics:
Circular

Size of Compatible Optics (mm):
25.0 - 25.4

Clear Aperture CA (mm):

22.0
Thickness of Compatible Optics (mm): 15.0 (Max)
Outer Diameter (mm): 64.0
Thickness (mm): 20.00
Travel (mm): ±1.5 in X and Y
Weight (g): 180
Construction: Black Anodized Aluminum
Contents of Kit: #62-956 , #16-460 , #15-849
Compatible Post: M6 x 1.0
Optical Axis Height (mm): 127.00
Post Diameter (mm): 25.4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
