

[See all 10 Products in Family](#)

25.0/25.4mm Optic Dia., 5 Axes Optical Mount



5 Axes Optical Mount



Stock #13-776 **5 In Stock**

⊖ 1 ⊕ €755.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€755,00 each
Qty 5-9	€717,60 each
Qty 10+	€642,10 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Adjustable - Linear (XYZ) & Tip-Tilt **Type:**

Circular **Type of Optics:**

Physical & Mechanical Properties

22.0 Clear Aperture CA (mm):

±2.0 in X and Y, ±1.5 in Z Travel (mm):

0.3 Weight (kg):

Black Anodized Aluminum Construction:

±2 Tip/Tilt Angle (°):

Threading & Mounting

25.0 - 25.4 Size of Compatible Optics (mm):

12.5 (Max) Thickness of Compatible Optics (mm):

M6 x 1.0 Compatible Post:

Regulatory Compliance

[Exempt](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Contains SVHC\(s\)](#) Reach 247:

Product Details

- 2-Axis, 3-Axis, and 5-Axis Adjustable Mounts Available
- Options for 12.5mm (0.5"), 25mm (1"), and 50mm (2") Dia. Optics
- M6 Mounting Threads

Multi-Axis Adjustable Optic Mounts can adjust optic positioning along the X- and Y-axes, as well as through optional Z-axis and Tip/Tilt adjustment. Compact packaging allows for fine alignment adjustments without the additional use of bulkier stages. Multi-Axis Adjustable Optic Mounts are ideal for alignment adjustments in prototyping and precision laboratory/benchtop optical systems. These mounts include M6 mounting threads making them compatible with our standard [Metric Stainless Steel Mounting Posts](#). A retainer ring and Delrin ring are used together to secure the optic without damaging its surface.

Technical Information

