

## 25.4mm Travel, Metric Micrometer, Thru-Hole 66.5mm Stage



Stock #55-464 3-4 DAYS

- 1 + **€1.193,00**

ADD TO CART

|           |
|-----------|
| Qty 1+    |
| €1.193,00 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:  
Linear (X)

Guide System:  
Ball Bearing

Type of Drive:  
Digital Micrometer (Metric)

Drive Orientation:  
Center Drive

Type:  
Metric

|                                                                             |
|-----------------------------------------------------------------------------|
| <b>Stage Size (mm):</b><br>66.5 x 66.5                                      |
| <b>Travel (mm):</b><br>25                                                   |
| <b>Construction:</b><br>Aluminum Top and Base/440C Stainless Steel Bearings |
| <b>Graduation (mm):</b><br>0.001                                            |
| <b>Load Capacity, Normal (kg):</b><br>28                                    |
| <b>Load Capacity, T<sub>a</sub> (kg):</b><br>4.5                            |
| <b>Load Capacity, T<sub>b</sub> (kg):</b><br>0.9                            |
| <b>Note:</b><br>Thru-Hole                                                   |
| <b>Stage Size (inches):</b><br>2.62 x 2.62                                  |
| <b>Straight Line Accuracy (μm):</b><br>2 per 25 mm of travel                |
| <b>Weight (g):</b><br>630                                                   |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |