

TECHSPEC® 25.4mm x -75mm FL, NIR I Imaging Grade PCV Cylinder Lens



TECHSPEC® Beam Shaping PCV Cylinder Lenses

Stock **#34-684** 3-4 DAYS

⊖ 1 ⊕ **€111,00**

ADD TO CART

Qty 1-5

€111,00

Qty 6+

€88,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.0/-0.025

Effective Focal Length EFL (mm):
-75.00

Substrate: □
[N-BK7](#)

f/#: 3
Numerical Aperture NA: 0.17
Coating: NIR I (600-1050nm)
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 600 - 1050
Back Focal Length BFL (mm): -77.31
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 22.86
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Edge Thickness ET (mm): 5.57
Radius R₁ (mm): 38.76
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <5
Power Axis Wedge (arcmin): <5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant