

## 25° Diffusing Angle 2" x 2" Unmounted Sheet



Stock **#65-887** CLEARANCE 3-4 DAYS

- 1 + **€242,50**

ADD TO CART

|         |
|---------|
| Qty 1-5 |
| €242,50 |

|         |
|---------|
| Qty 6+  |
| €206,25 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

### Get Product Downloads

Angle Tolerance (°):  
±2.5

Diffusing Angle (°):  
25 (FWHM)

Dimensional Tolerance (mm):  
±0.5

Dimensions (inches):

|                                                                                                     |
|-----------------------------------------------------------------------------------------------------|
| 2 x2                                                                                                |
| <b>Dimensions (mm):</b><br>50.80 x 50.80                                                            |
| <b>Operating Temperature (°C):</b><br>-30 to +100 (Maximum of 240 Hours)                            |
| <b>Substrate:</b> <input type="checkbox"/><br>Polycarbonate                                         |
| <b>Thickness (mm):</b><br>0.78                                                                      |
| <b>Transmission (%):</b><br>>85                                                                     |
| <b>Type:</b><br>Holographic Diffuser                                                                |
| <b>Wavelength Range (nm):</b><br>400 - 700                                                          |
| <b>Width (mm):</b><br>50.80                                                                         |
| <b>Construction:</b><br>Unmounted                                                                   |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>0.22 J/cm² @ 1064nm, 10ns (typical) |
| <b>Length (mm):</b><br>50.80                                                                        |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |