

TECHSPEC® 25mm Aluminized, Half-Penta Prism



Stock #65-590 3-4 DAYS

⊖ 1 ⊕ **€180,00**

ADD TO CART

Qty 1-5
€180,00

Qty 6+
€144,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
VIS 0° & Aluminized

Substrate: ☐
[N-BK7](#)

Height (mm):
35.35

Surface Quality: 40-20
Type: Half-Penta Prism
Dimensional Tolerance (mm): ±0.10
Angle Tolerance (arcmin): ±3
Bevel: Protective bevel as needed
Image Orientation: Right-Handed
Coating Specification: Entrance/Exit Faces: R _{avg} ≤0.4% @ 425 - 675nm Reflecting Surface: R _{avg} >85% @ 400 - 700nm w/Black Overpaint
Ray Deviation (°): 45
Wavelength Range (nm): 425 - 675
Surface Flatness (P-V): λ/2
Width (mm): 25.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View