

# 2.5mm CA, A-25H0-P10 Corning® Varioptic® Variable Focus Liquid Lens, Packaged A-Series, 6 pins FPC with Thermistor



2.5mm CA, A-25H0-P10 Corning® Varioptic® Variable Focus Liquid Lens, Packaged A-Series, 6 pins FPC with Thermistor



Stock **#15-739** CLEARANCE 3-4 DAYS

- 1 + **€81,95**

ADD TO CART

|        |
|--------|
| Qty 1+ |
| €81,95 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



|                        |
|------------------------|
| Diameter (mm):<br>9.40 |
| Coating:<br>VS         |

|                                                                                                                                               |
|-----------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Type:</b><br>Packaged Lens w/ Thermistor                                                                                                   |
| <b>Clear Aperture CA (mm):</b><br>2.5                                                                                                         |
| <b>Contents of Kit:</b><br>Packaged A-25H0 with a straight flex cable with thermistor FPC-A-10 (6 pins)                                       |
| <b>Focus Range:</b><br>-5 to +13 diopter                                                                                                      |
| <b>Model Number:</b><br>A-25H0-P10                                                                                                            |
| <b>Operating Temperature (°C):</b><br>-30 to +85                                                                                              |
| <b>Storage Temperature (°C):</b><br>-40 to +85                                                                                                |
| <b>Thickness (mm):</b><br>3.50                                                                                                                |
| <b>Transmission (%):</b><br>97 @ 587nm                                                                                                        |
| <b>Transmitted Wavefront Error, RMS:</b><br>30nm                                                                                              |
| <b>Typical Applications:</b><br>Compact optical systems such as barcode readers, industrial cameras, & medical imaging and biometrics systems |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 224:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |