

TECHSPEC®

25mm CA Series Fixed Focal Length Lens



25mm CA Series Fixed Focal Length Lens

Stock #11-318 3-4 DAYS



1



€910,00

ADD TO CART

Qty 1+

€910,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Iris Option:
Variable

Length (mm):
93.65

Horizontal Field of View, 2/3" Sensor:
20.2°

Filter Thread:
M52 x 0.75

Maximum Diameter (mm): 52
Maximum Rear Protrusion (mm): 0
Horizontal Field of View, 1" Sensor: 29.2°
Maximum Image Circle (mm): 27.90
Numerical Aperture NA, Object Side: 0.019
Horizontal Field of View, 4/3" Sensor: 38.0°
Horizontal Field of View, 1.1" Sensor: 32.1°
Number of Elements (Groups): 10 (9)
Type: Fixed Focal Length Lens
Focal Length FL (mm): 25.00
Primary Magnification PMAG: 0.112
Maximum Sensor Format: APS-C
Working Distance (mm): 200 - ∞
Mount: TFL-Mount
Aperture (f/#): f/2.8 - f/16
Coating Specification: N4 MgF₂
Entrance Pupil Position (mm): 39.64
Object Space Principal Plane (mm): 47.46
Image Space Principal Plane (mm): -8.15
Field of View at Max Sensor Format: Horizontal: 50.0° Vertical: 38.0° Diagonal: 61.5°
Maximum Distortion (%): 5.80
Horizontal Field of View, APS-C Sensor: 50.0°
Exit Pupil Position (mm): -56.88
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant