

2.5mm CA, VIS Coated, 70 Diopter Focus Range, A-P-25H0-D0-33 Corning® Varioptic® Variable Focus Liquid Lens, Packaged A-Series, 6 pins FPC with Thermistor



Corning® Varioptic® Variable Focus Liquid Lenses



Stock #28-777 NEW ☐ In Stock

-

1

+

€135,00

ADD TO CART

Qty 1-10
€135,00

Qty 11+
€121,50

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):

8.80
Coating: VS
Type: Packaged Lens w/ Thermistor
Clear Aperture CA (mm): 2.5
Contents of Kit: Packaged A-25H0-D0 with a straight flex cable with thermistor FPC-A-33 (6 pins)
Focus Range: -35 to +35 diopter
Model Number: A-P-25H0-D0-33
Operating Temperature (°C): -20 to +60
Storage Temperature (°C): -40 to +85
Thickness (mm): 2.80
Transmission (%): 97 @ 587nm (typical)
Transmitted Wavefront Error, RMS: 70nm
Typical Applications: Very close auto-focus or continuous auto-focus applications in portable devices and in laser or lighting applications for variable focus and expansion control. Features 3X higher dynamic range over the A-25HX lens.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
