

TECHSPEC®

25mm Dia., 0.25 Numerical Aperture, 350-700nm Coated, Inked, High Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#16-957-INK** [CONTACT US](#)

[Other Coating Options](#)



1



€365,00

ADD TO CART

Qty 1-5

€365,00

Qty 6+

€292,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 ±0.025

Effective Focal Length EFL (mm):

50.00 @ 587.6nm
Numerical Aperture NA: 0.25
Back Focal Length BFL (mm): 45.23
Substrate: ☐ N-BK7
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: VIS-EXT+ (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm @ ±30° AOI R _{abs} <1.5% @ 350 - 700nm @ ±30° AOI
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 24.00
Edge Thickness ET (mm): 4.14
Center Thickness CT (mm): 7.24 ±0.10
f#: 2.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View