

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #17-419 3-4 DAYS



1



€350,00

ADD TO CART

Qty 1-5

€350,00

Qty 6+

€280,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):
25.00 @ 1550nm

Numerical Aperture NA:
0.5

Back Focal Length BFL (mm): 18.97 @ 587.6nm
Substrate: ☐ N-SF6
Aspheric Design Wavelength (nm): 1550
Coating: Uncoated
Centering (arcmin): <2.5
Surface Quality: 40-20
Clear Aperture CA (mm): 22.5
Edge Thickness ET (mm): 4.25
Center Thickness CT (mm): 8.50 ±0.1
f#: 1
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Conjugate Distance: Infinite
Asphere Figure Error, @ 632.8nm: 0.4λ RMS and 2λ PV
Power (diopters): 40.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View