

TECHSPEC® 25mm Dia., 0.50 NA, Uncoated, Calibration Grade Aspheric Lens



Calibration Grade Aspheric Lenses

Stock **#69-142** 3-4 DAYS



1



€455,00

ADD TO CART

Qty 1-5

€455,00

Qty 6+

€410,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
25.00 @ 587.6nm

Numerical Aperture NA:
0.50

Back Focal Length BFL (mm): 20.28
Substrate: L-BAL35
Aspheric Design Wavelength (nm): 587.6
Coating: Uncoated
Centering (arcmin): ≤1
Surface Quality: 20-10
Clear Aperture CA (mm): 22.00
Edge Thickness ET (mm): 1.74
Center Thickness CT (mm): 7.50
f/#: 1.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 330 - 2400
Conjugate Distance: Infinite
Asphere Figure Error, @ 632.8nm: 1.6λ RMS and 6λ PV
Power (diopters): 40.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View