

**TECHSPEC® 25mm Dia., 0.66 NA, Uncoated, Calibration Grade Aspheric Lens**



Calibration Grade Aspheric Lenses

Stock **#69-141** 3-4 DAYS



1



€455,00

ADD TO CART

Qty 1-5

€455,00

Qty 6+

€410,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Diameter (mm):**  
25.00 +0.0/-0.1

**Effective Focal Length EFL (mm):**  
18.75 @ 587.6nm

**Numerical Aperture NA:**  
0.66

|                                                        |
|--------------------------------------------------------|
| Back Focal Length BFL (mm):<br>12.46                   |
| Substrate: <a href="#">L-BAL35</a>                     |
| Aspheric Design Wavelength (nm):<br>587.6              |
| Coating:<br>Uncoated                                   |
| Centering (arcmin):<br>≤1                              |
| Surface Quality:<br>20-10                              |
| Clear Aperture CA (mm):<br>22.00                       |
| Edge Thickness ET (mm):<br>1.63                        |
| Center Thickness CT (mm):<br>10.00                     |
| f/#:<br>0.76                                           |
| Bevel:<br>Protective bevel as needed                   |
| Shape of Back Surface:<br>Plano                        |
| Type:<br>Aspheric Lens                                 |
| Wavelength Range (nm):<br>330 - 2400                   |
| Conjugate Distance:<br>Infinite                        |
| Asphere Figure Error, @ 632.8nm:<br>1.6λ RMS and 6λ PV |
| Power (diopters):<br>53.33                             |

Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS:<br><a href="#">Compliant</a>                  |
| Certificate of Conformance:<br><a href="#">View</a> |