


**TECHSPEC® 25mm Dia., 532nm, Stemmed Laser Mirror**



Stock #17-557 CLEARANCE CONTACT US

- 1 + **€173,00**

ADD TO CART

Qty 1-5

€173,00

Qty 6+

€138,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Clear Aperture CA (mm):**  
22.50

**Coating:**  
Laser Mrror (532nm)

|                                                                                 |
|---------------------------------------------------------------------------------|
| <div>Design Wavelength DWL (nm):<br/>532</div>                                  |
| <div>Diameter (mm):<br/>25.00 +0.00/-0.10</div>                                 |
| <div>Substrate: <div>Fused Silica (Coming 7980)</div></div>                     |
| <div>Surface Quality:<br/>10-5</div>                                            |
| <div>Thickness (mm):<br/>13.00 ±0.20</div>                                      |
| <div>Type:<br/>Stemmed Mirror</div>                                             |
| <div>Clear Aperture (%):<br/>90.00</div>                                        |
| <div>Back Surface:<br/>Commercial Polish</div>                                  |
| <div>Coating Specification:<br/>R<sub>abs</sub> &gt;99.8% @ 532nm</div>         |
| <div>Surface Flatness (P-V):<br/>λ/10</div>                                     |
| <div>Coating Type:<br/>Dielectric</div>                                         |
| <div>Damage Threshold, Reference: <div>10J/cm² @ 20ns, 20Hz @ 532nm</div></div> |
| <div>Edges:<br/>Ground, protective bevel as needed</div>                        |
| <div>Stem Diameter (mm):<br/>12.50 +0.00/-0.10</div>                            |
| <div>Compatible Kinematic Mount:<br/><a href="#">#58-853</a></div>              |
| <div>Stem Length (mm):<br/>6.50 ±0.20</div>                                     |

## Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS:<br/><a href="#">Compliant</a></div>                  |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |