

**TECHSPEC® 25mm Dia., Enhanced Aluminum,  $\lambda/10$  Stemmed Mirror**



TECHSPEC® Stemmed Mirror



Stock **#14-579** CLEARANCE 3-4 DAYS

- 1 +

**€132,00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| €132,00                       |
| Qty 6+                        |
| €105,00                       |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
25.00 +0.00/-0.10

Surface Flatness (P-V):

|                                                                     |
|---------------------------------------------------------------------|
| N10                                                                 |
| <b>Substrate:</b> <a href="#">Fused Silica</a> (Coming 7980)        |
| <b>Back Surface:</b><br>Commercial Polish                           |
| <b>Surface Quality:</b><br>20-10                                    |
| <b>Coating Specification:</b><br>R <sub>avg</sub> >95% @450 - 650nm |
| <b>Coating:</b><br>Enhanced Aluminum (450-650nm)                    |
| <b>Coating Type:</b><br>Metal                                       |
| <b>Clear Aperture (%):</b><br>90.00                                 |
| <b>Edges:</b><br>Ground, protective bevel as needed                 |
| <b>Thickness (mm):</b><br>13.00 ±0.20                               |
| <b>Type:</b><br>Stemmed Mirror                                      |
| <b>Wavelength Range (nm):</b><br>450 - 650                          |
| <b>Compatible Kinematic Mount:</b><br><a href="#">#58-853</a>       |
| <b>Stem Diameter (mm):</b><br>12.50 +0.00/-0.10                     |
| <b>Stem Length (mm):</b><br>6.50 ±0.20                              |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |