

TECHSPEC® 25mm Dia., Protected Silver, λ /10 Stemmed Mirror



TECHSPEC® Stemmed Mirror



Stock **#14-582** CLEARANCE 3-4 DAYS

- 1 +

€153,00

ADD TO CART

Qty 1-5
€153,00
Qty 6+
€122,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Surface Flatness (P-V):

N/10

Substrate: [Fused Silica](#) (Coming 7980)

Back Surface:
Commercial Polish

Surface Quality:
20-10

Coating Specification:
R_{avg} >98% @450 - 2000nm
R_{avg} >98% @2000 - 10,000nm

Coating:
Protected Silver (450-10000nm)

Coating Type:
Metal

Clear Aperture (%):
90.00

Edges:
Ground, protective bevel as needed

Thickness (mm):
13.00 ±0.20

Type:
Stemmed Mirror

Wavelength Range (nm):
450 - 10000

Compatible Kinematic Mount:
[#58-853](#)

Stem Diameter (mm):
12.50 +0.00/-0.10

Stem Length (mm):
6.50 ±0.20

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)