

TECHSPEC® 25mm Dia. Uncoated, λ /10 Fused Silica Window



TECHSPEC® Uncoated Laser Window Substrates

Stock **#48-023** 3-4 DAYS

⊖ 1 ⊕ **€150,00**

ADD TO CART

Qty 1-5

€150,00

Qty 6+

€135,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Clear Aperture CA (mm):
22.50

Coating:
Uncoated

Diameter (mm): 25.00 +0.00/-0.10
Substrate: Fused Silica Excimer Grade (Corning 7980 KrF)
Index of Refraction n_d: 1.458
Surface Quality: 10-5
Thickness (mm): 3.00 ±0.10
Type: Laser Line Window
Bevel: Protective as needed
Clear Aperture (%): 90
Transmitted Wavefront, P-V: $\lambda/10$
Abbe Number (v_d): 67.8
Parallelism (arcsec): ≤5
Wavelength Range (nm): 200 - 2200
Fused Silica Grade: 7980 KrF 0A
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View