

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

25mm Dia X -103.36mm FL Enhanced Aluminum Coated, Convex Mirror



Stock #64-064 3-4 DAYS

-

1

+

 €45,50

ADD TO CART

Qty 1-5
€45,50
Qty 6+
€41,00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.10

Focal Length FL (mm):
-104.60

Center Thickness CT (mm):
3.20

Clear Aperture (%):

Coating:
Enhanced Aluminum (450-650nm)

Coating Specification:
R_{avg} >95% @ 450 - 650nm

Coating Type:
Metal

Edge Thickness ET (mm):
2.83

Focal Length Tolerance (%):
±2

Radius R (mm):
209.20

Substrate: 
[N-K5](#)

Surface Quality:
60-40

Type:
Spherical Mirror

Wavelength Range (nm):
450 - 650

Damage Threshold, Reference: 
0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)
