

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #19-517 3-4 DAYS

[Other Coating Options](#)



1



€37,00

ADD TO CART

Qty 1-10

€37,00

Qty 11+

€33,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.2

Effective Focal Length EFL (mm):
25.00

Numerical Aperture NA:
0.50

Back Focal Length BFL (mm): 19.4
Substrate:  H-K51
Focal Length Tolerance (%): ±5
Coating: Uncoated
Centering (arcmin): ≤30
Surface Quality: 80-50 (typical)
Clear Aperture CA (mm): 22.5
Edge Thickness ET (mm): 1.81
Center Thickness CT (mm): 8.50 ±0.30
f/#: 1
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 25
Radius R ₂ (mm): ∞
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 350 - 2000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View