

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

25mm Dia. X 25mm FL Protected Gold, Concave Mirror



Stock #43-835 3-4 DAYS

- 1 + €58,00

ADD TO CART

Qty 1-49

€58,00

Qty 50+

€49,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: ☐ [N-BK7](#)

Focal Length Tolerance (%):
±2

Surface Quality:
80-50

Diameter (mm):

25.00 ±0.50
Effective Focal Length EFL (mm): 25.00
Radius of Curvature (mm): 50.00
Aperture (f/#): f/1
Coating: Protected Gold (700-10000nm)
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating Type: Metal
Clear Aperture (%): 90
Edge Thickness ET (mm): 3.0
Radius R₁ (mm): 50.00
Thickness Tolerance (mm): ±0.5
Type: Spherical Mirror
Wavelength Range (nm): 700 - 10000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant